

BRADY B-7797 AUTO-DISPENSABLE GLOSSY WHITE THERMAL TRANSFER PRINTABLE POLYIMIDE LABEL STOCK

TDS No. B-7797
Effective Date: 11/20/2023

Description:

GENERAL

Print Technology: Thermal transfer

Material Type: White polyimide

Finish: Glossy

Adhesive: Permanent acrylic

APPLICATIONS

Printed circuit board and electronic component pre-process labeling, especially with auto-dispensing requirements.

RECOMMENDED RIBBONS

- Brady Series R4900A
- Brady Series R6000 Halogen Free
- Brady Series R6300
- Brady Series R8965
- Brady Series RR103

REGULATORY/AGENCY APPROVALS

UL: Brady B-7797 is a UL Recognized Component to UL969 Labeling and Marking Standard when printed with the Brady Series R6300 and Brady Series R6000 Halogen Free ribbons. See UL file MH17154 for specific details. UL information can be accessed on-line at UL.com in the UL Product iQ area.

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

- In Canada: www.bradycanada.ca/weee-rohs
- In Europe: www.bradyeurope.com/rohs
- In Japan: www.brady.co.jp/products/labelsuse/rohs
- All other regions: www.bradyid.com/weee-rohs

SPECIAL FEATURES

B-7797 is designed for auto-dispense applications.

B-7797, in combination with the Series R6300 ribbon or R6000 Halogen Free ribbon, meets the requirements of MIL-STD-202G, Method 215K.

B-7797 is designed to withstand multiple cycles of harsh condition washes for printed circuit boards.

The R4900A, R6300 and R8965 ribbons are recommended for use in non reflow applications for aqueous cleaning.

Details:

PHYSICAL PROPERTIES	TEST METHODS	TYPICAL RESULTS
Thickness	ASTM D1000 -Substrate (topcoat and film) -Adhesive -Total (excluding liner)	0.0024 inch (0.061 mm) 0.0013 inch (0.033 mm) 0.0037 inch (0.094 mm)
Adhesion to: -Stainless Steel -Epoxy PC Board	ASTM D1000 20 minute dwell 24 hour dwell 20 minute dwell 24 hour dwell	45 oz/in (49 N/100 mm) 56 oz/in (61N/100 mm) 35 oz/in (38 N/100 mm) 48 oz/in (52 N/100 mm)
Tack	ASTM D2979 Polyken™ Probe Tack 0.5 second dwell	42 oz(1200 g)
Drop Shear	PSTC-7 (1/2" x 1" sample)	> 100 hours

Dielectric Strength	ASTM D1000	12,000 volts
---------------------	------------	--------------

Performance properties tested on B-7797 printed with the Brady Series R6300 thermal transfer ribbon. Printed samples of B-7797 were laminated to aluminum and allowed to dwell 24 hours before exposure to the indicated environmental conditions.

PERFORMANCE PROPERTIES	TEST METHODS	TYPICAL RESULTS
Short Term High Service Temperature	80 seconds at various temperatures	No visible effect to label at 572° F (300°C) and 626°F (330°C), label discolors slightly but still functional, at 662°F (350°C). Print is still legible.
	5 minutes at various temperatures	No visible effect to label at 500°F (260°C), label discolors slightly at 536°F (280°C), moderately discolors at 572°F (300°C) but remains functional. Print is still legible.
	2 hours at various temperatures	No visible effect to label at 338°F (170°C) and 392°F (200°C). Label discolors slightly at 446°F (230°C), moderately at 500°F (260°C), but remains functional. Print is still legible.
Long Term High Service Temperature	1000 hours at various temperatures	Label discolors slightly at 248°F (120°C), and discolors moderately at 293°F (145°C), but remains functional. Print is still legible.
Low Service Temperature	1000 hours at -112°F (-80°C)	No visible effect
Humidity Resistance	1000 hours at 100°F (37°C)/95%RH	No visible effect
UV Light Resistance	ASTM G155, cycle 1, Dry 1000 hours in Q-Sun Xenon Test Chamber	No visible effect
Weatherability*	ASTM G155, Cycle 1 1000 hours in Xenon arc Weather-Ometer®	No visible effect
Salt Fog Resistance	ASTM B117 1000 hours in 5% salt fog solution chamber	No visible effect
Abrasion Resistance	Taber Abraser, CS-10 grinding wheels, 250 g/arm (Fed. Std. 191A, Method 5306)	Print legible up to 50 cycles with the R6300 Ribbon Print legible up to 100 cycles with the R6000 Halogen Free Ribbon
Chemical Vapor Phase Resistance	Labels adhered to epoxy PC board and exposed to the vapor of the boiling chemical for 10 minutes and then rubbed with a cotton swab saturated with the chemical for 10 rubs Test samples were baked 4 minutes at 160°C prior to testing Micronox® MX2501	Severe print removal

*B-7797 is not recommended for outdoor use.

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
----------------------	---------------------

Test samples were printed with the Brady Series R6300 and R6000 Halogen Free ribbons. Labels were adhered to an epoxy PC board. Test samples were exposed to the indicated environments. All test samples were immersed in the test fluids for 10 minutes prior to rubbing with a cotton swab ten times. Note: Samples were tested without exposure to reflow conditions.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE				
	EFFECT TO LABEL	R6300		R6000 Halogen Free	
		WITHOUT RUB	WITH RUB	WITHOUT RUB	WITH RUB

Kyzen Corp, 15% Aquanox® A4625 at 140°F (60°C)	No visible effect	1	1	1	5
Kyzen Corp, 7% Aquanox® A4382 at at 150°F (65°C)	No visible effect	1	1	1	5
Kyzen Corp, 10% Aquanox® A4638 at 145°F (63°C)	No visible effect	1	1	1	1
Zestron, 15% Atron® AC205 at 150°F (65°C)	No visible effect	1	1	3	5
Zestron, 15% Atron® AC207 at 150°F (65°C)	No visible effect	1	1	5	5
Zestron, 15% Vigon® A201 at 150°F (65°C)	No visible effect	1	2	1	5
Zestron, 15% Vigon® N600 at 150°F (65°C)	No visible effect	1	1	1	5
Isopropyl Alcohol 99% at 180°F (82°C)	No visible effect	1	1	1	2
Deionized water at 212°F (100°C)	No visible effect	1	1	1	1

Rating Scale:

1=no visible effect

2=slight smear or print removal, detectable but minimal smear

3=moderate smear or print removal (print still legible)

4=severe smear or print removal (print illegible or just barely legible)

5=complete print removal

PERFORMANCE PROPERTY	TEST METHOD
Solvent Resistance	MIL-STD-202G, Method 215K

Test samples were printed with the Brady Series R6300 and R6000 Halogen Free ribbons. Labels were printed with alphanumeric and barcodes. Test samples were subjected to 3 cycles of 3 minute immersions immediately followed by a toothbrush rub after each immersion.

TEST FLUID	RESULTS R6300	RESULTS R6000 Halogen Free
Solvent A 1 part IPA, 3 parts mineral spirits	Meets requirement	Meets requirement
Solvent C Terpene Defluxer	Meets requirement	Meets requirement
Solvent D Saponifier @ 70°C	Meets requirement	Meets requirement

Shelf Life:

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual applications.

Trademarks:

ANSI: American National Standards Institute (U.S.A.)

ASTM: American Society for Testing and Materials (U.S.A.)

All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units

Aquanox® is a registered trademark of the Kyzen Corporation

Atron® is a registered trademark of the Zestron Corporation

Micronox® is a registered trademark of the Kyzen Corporation

PSTC: Pressure Sensitive Tape Council (U.S.A.)

Polyken™ is a trademark of Testing Machines Inc.

UL: Underwriters Laboratories Inc. (U.S.A.)

Vigon® is the registered trademark of Zestron Corporation

Weather-Ometer® is a registered trademark of Atlas Material Testing Technology LLC

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2023 W.H. Brady, N.V. | All Rights Reserved

Material may not be reproduced or distributed in any form without written permission.

Brady Europe | Industriepark C3 Lindestraat 20 | B9240 Zele | Belgium | Tel: +32 52.45.7811 | Fax: +32 52.45.7812